

## Spesifikasjoner Parasound JC2 BP

### **Frequency Response**

5 Hz - 100 kHz, +0/-3 dB **Distortion**

THD: < 0.003% at 100 Hz

THD: < 0.005% at 20 kHz

IM: < 0.003% **S/N Ratio**

> 116 dB, input shorted, IHF A-weighted

> 104 dB, input shorted, unweighted **Crosstalk**

> 100 dB at 10 kHz

> 90 dB at 20 kHz **Gain**

14 dB, maximum **L, R Gain Control Range**

- 10 dB **Input Impedance**

Unbalanced: 30k ohms

Balanced: 30k ohms per leg **Output Impedance**

Unbalanced: < 60 ohms

Balanced: < 60 ohms per leg **Input Sensitivity**

200 mV for 1 V output

Total Gain: 14 dB

Maximum Output: 8 V **XLR Pin Identification**

1 = Ground (Shield)

2 = Positive

3 = Negative (Return)

### **AC Power Requirement**

110 - 120 V or 220-240 V, 50 - 60 Hzs

(Set AC Voltage switch on rear panel)

25 watt standby; 30 watts when turned on **Dimensions**

Width: 17 1/4" (437 mm)

Depth: 16" (406 mm)

Height, with feet: 5 7/8" (150 mm)

Height, without feet: 5 1/4" (133 mm) **Weight**

Net: 24 lbs. (11 kg)

Shipping: 36 lbs. (16.4 kg) **Rack Mount Accessory**

HRA 3 (May be purchased separately)